

Service Bulletin

					Bulletin No. 2011-02
Circulate to:	Sales Manager	Accounting	Service Manager	Technician	Parts Manager

R3, X3 Wiring Diagrams

Models Affected

Model	Model Number	
R3-30	940100070	
R3-40	940100020	
R3-45	940100030	
R3-55	940100050	
X3-45	940200010	
X3-55	940200020	

Description

New rotary switch wiring diagrams for the R3 and X3 series trolling motors.

Wire Color Code Abbreviations


Wire Color Abbreviations							
BLK	Black		BLU	Blue			
BRN	Brown] [GRY	Gray			
GRN	Green] [ORN or ORG	Orange			
PNK	Pink	[PPL or PUR	Purple			
RED	Red		TAN	Tan			
WHT	White] [YEL	Yellow			
LT or LIT	Light		DK or DRK	Dark			

THE INFORMATION IN THIS DOCUMENT IS CONFIDENTIAL AND PROTECTED BY COPYRIGHT AND IS THE PROPERTY OF MERCURY MARINE.


This document is provided for the sole and exclusive use of the original recipient as prescribed by Mercury Marine and may not be distributed or copied, digitally or otherwise, without the prior written consent of Mercury Marine.

Correction

New product has been released. See the diagram below for the proper wire locations.



- a Rotary switch
- **b** Blue lead (terminal 2) (to motor)
- c Black negative battery lead
- **d** Black lead (to brush card)
- e Black/red positive battery lead
- **f** Yellow lead (terminal 3) (to motor)
- g Red lead (terminal 1) (to motor)



- a Rotary switch
- **b** Blue lead
- c Black negative battery lead
- **d** Black lead (with insulator sleeve)
- e Black/red positive battery lead
- f Yellow lead
- g Red lead

 $\hbox{THE INFORMATION IN THIS DOCUMENT IS CONFIDENTIAL AND PROTECTED BY COPYRIGHT AND IS THE PROPERTY OF MERCURY MARINE. } \\$

This document is provided for the sole and exclusive use of the original recipient as prescribed by Mercury Marine and may not be distributed or copied, digitally or otherwise, without the prior written consent of Mercury Marine.

Page 2 / 2 © 2011 Mercury Marine NOVEMBER 2011 2011-02